


technics



Name	Reference	Current
Holon 40 directional surface mounted	KR96220x	700mA
Holon 40 directional surface mounted	KR96230x-XXXX-XX	700mA

1 dimensions



2 important remark

holon 40 directional surface mounted is gear exclusive, the gear however cannot be installed above the holon on the hollow ceiling. due to the dimensions of the fixture and the position of the installation screws, there's no space left for a throughput hole for the gear. so make sure the driver is placed at a distance where it still can be reached in case of a problem


Please make sure that main voltage is disconnected before proceeding!

Remark:
in case of using a standard junction box or in case of installation on concrete ceiling, the accessory KR76250x can be used. check the manual delivered with KR76250x for more information


3 installation




the mold that's delivered within the packaging can be used to indicate the fixation holes on the ceiling




drill three holes of Ø5mm (depth min. 40mm) for the plugs and one hole in the middle of ±18mm for the cable throughput



insert the plugs in the holes pull the connection cables through




pull the connection cables through the hole in the middle of the installation part and fix it with 3 screws



mind the polarity!
red = plus
black = minus


connect the wires to the connectors included in the fixture. Add the red wire to the connector with the red wire coming from the LED, add the black wire to the connector with the black wire coming from the LED



fix the rest of the fixture by screwing it onto the installation part




once the holon is completely installed it can be inclined in any angle up to 90° by pulling the tube



installation

kreon

technics






installation

it can also be rotated for 330°

KR762000

KR762100

KR762200



4 accessories

in case of accessories
check the manual KR8622102021 delivered with the accessory
only one accessory per holon



5 pictures

kreon nv

Industrieweg Noord 1152
3660 Opglabbeek
Belgium

Tel + 32 89 81 97 80
Fax + 32 89 81 97 90

www.kreon.com
mailbox@kreon.be

revision date: 28/07/2016
KR8622002067

Sheet 2/2